



Only 120g *Light As Cloud*

LEDEX™ WL-070

Combo of Cordless & Cord types




ADVANTAGES

Simple Operations

Clear display, simple function including ramp mode, easy to use.

10 sec. Fast Cure

Use high power 5W LED, it can cure the composites over 3mm in 10 sec.



Never Shutdown Within Continuous Use

Smart heat-management system prevents device over-heating during continuous use.

Combo Of Cordless & Cord Types

When curing light run out of batteries, can also be plugged in and used as a corded light.



Variety Of Optical Fiber Light Guide Rod

There are 3,5,8 mm black or transparent optical fiber light guide rod can be applied.



Specification

Handpiece		Battery	Type	Lithium-ion, 3.7 V/800 mAh
Light source	High power dental blue 5 W LED, average lifespan is 100,000 hours		Charge time	About 2 hours
Wavelength	440-480 nm, peak:460 nm		Use time	40 Minutes (240 times in 10 Sec. mode)
Radiant intensity	1000 mW/cm ² above	Power Supply	Type	Mini USB jack
Light guide rod	Ø8mm optical fiber, Sterilizable in autoclave		Input	100-240 V, 50/60 Hz
Weight	120 g (with battery & lightguide rod)		Output	DC 5 V/2 A
Dimensions	Ø 26 (max) x L156 mm			

